



ZA de l'Arceau  
49300 LE PUY SAINT BONNET  
Tel : +33 2 41 56 46 00  
Fax : +33 2 41 56 46 10  
www.mcd-fr.com

Au Puy, Le 21 Novembre 2008

To the technical department

**Object : Modification N° 6 « Wheel Modification ».**

Dear customer,

We inform you about the modification of our wheel to guide the shutter to his roller.

We use actually a simple extrusion wheel covered with self-adhesive foam used to guide the shutter out of the tracks to his roller as well as reduce the noise when opening and closing the shutter. We noted in use that this self-adhesive foam sometimes came to unstick from his wheel. To prevent stop this trouble, we decided to create a new bi extrusion wheel mould with stiff PVC for the inside of the wheel and supple for the outside to obtain the same reduction of noise than before without unstik material. The dimensions of this new wheel don't change to respect compatibility of the both in case of after sale.

Since the week 49, all the MCD's shutter will be equipped with this new wheel (*Cf.picture 1*) changing our old wheel equipped with the self-adhesive foam (*Cf.picture 2*).

Best regards.

MCD's team



*Picture 1*  
*New wheel*



*Picture 2*  
*Old wheel with self-adhesive foam*